

# ONTEC G E1E 180 M AT I TM-OG.EEATM800I



No: 03A25



No: 4420/2021  
Valid until:  
05.09.2026



No: 88-128652



No:  
B\_BK\_60112\_0425\_2024  
Valid until:  
24.01.2030



No: 03A25



No: 2291559.02-  
UAE  
Valid until:  
05.11.2026



No: 03A25




No: DIT\_001



No: V1.19



|                                            |                                                         |
|--------------------------------------------|---------------------------------------------------------|
| Producer                                   | <b>TM Technologie</b>                                   |
| Category                                   | <b>emergency luminaires</b>                             |
| Application                                | <b>evacuation route direction</b>                       |
| Family                                     | <b>ONTEC G</b>                                          |
| Colour/Colour - RAL                        | <b>blue , RAL5015</b>                                   |
| Colour structure                           | <b>matte , satin, smooth</b>                            |
| Version                                    | <b>autotest</b>                                         |
| Operating mode                             | <b>M</b>                                                |
| Duration time                              | <b>3 h</b>                                              |
| Protection degree                          | <b>IP20</b>                                             |
| Impact protection degree                   | <b>IK05</b>                                             |
| Appliance classes                          | <b>II</b>                                               |
| Material                                   | <b>plastic</b>                                          |
| Installation method*                       | <b>surface, flush-mounted, suspended, wall, ceiling</b> |
| Adapted to use a pictogram                 | <b>yes</b>                                              |
| Pictogram included                         | <b>yes</b>                                              |
| Pictogram dimensions                       | <b>125x125 mm</b>                                       |
| Evacuation sign dimensions                 | <b>250x125 mm</b>                                       |
| Pictogram type                             | <b>foil</b>                                             |
| Graphic number                             | <b>K6</b>                                               |
| Pictogram logo                             | <b>TM Technologie</b>                                   |
| Luminous flux                              | <b>&gt;350 cd/m<sup>2</sup></b>                         |
| Visibility                                 | <b>25 m</b>                                             |
| Colour temperature                         | <b>5700 K</b>                                           |
| Nominal voltage AC                         | <b>210-250 V</b>                                        |
| Nominal voltage DC                         | <b>- V</b>                                              |
| Light source                               | <b>LED</b>                                              |
| Maximum light power                        | <b>0.9 W</b>                                            |
| LED lifetime                               | <b>50000 h</b>                                          |
| Minimum temperature                        | <b>+10 °C</b>                                           |
| Maximum temperature                        | <b>+35 °C</b>                                           |
| Battery                                    | <b>LiFePO4/C (LN) 3.2V 1.5-1.6Ah</b>                    |
| Warranty (body, electronics, light source) | <b>36 months</b>                                        |
| Net dimensions <b>L x W x H</b> [±2 mm]    | <b>251 mm x 29 mm x 198 mm</b>                          |



\* Some of mounting methods are possible only with additional accessory dedicated for that product.